

## DF 110

### Detector of refrigerant gases and hydrogen (H<sub>2</sub>)

#### KEY POINTS

- Detection of all the HCFC and HFC refrigerants
- Detection of mixtures 5% hydrogen - 95% nitrogen (Nidron 5...)
- Heated diode sensor
- 3 modes of sensitivity (high, low and normal)
- Manual and automatic autozero

#### TECHNICAL FEATURES

<b>Detected gases</b>	<b>HFC:</b> R134a, R404a, R407c, R410a, R32, R422a/b/c/d, R425a, R507a, R125 <b>HCFC:</b> R22 <b>CFC:</b> R12, R502 <b>Others:</b> H <sub>2</sub> , R290, R600a, HFO-1234yf, HFO-1234ze
<b>Measuring element</b>	Semi-conductor sensor
<b>Display</b>	13 leds: - 8 for the graphic visualization of thresholds - 3 for the sensitivity of detection - 2 for the battery level and manual autozero
<b>Indication</b>	LED: gradual lighting up when the gas concentration increases Audible : the beep frequency increases when the gas concentration increases
<b>Probe</b>	Flexible, 300 mm length
<b>Autonomy</b>	> 12 hours
<b>Housing</b>	Anti-choc ABS, protection IP54
<b>Keypad</b>	3 keys
<b>European directives</b>	2014/30/EU EMC ; 2014/35/EU Low Voltage ; 2011/65/EU RoHS II ; 2012/19/EU WEEE
<b>Power supply</b>	4 AAA LR03 1.5 V batteries
<b>Ambiance</b>	Neutral gas
<b>Conditions of use (°C, %RH, m)</b>	From 0 to +50 °C. In non condensing conditions. From 0 to 2000 m.
<b>Storage temperature</b>	From -20 to +80 °C
<b>Auto-extinction</b>	15 min
<b>Weight</b>	295 g

#### SPECIFICATIONS

Mode	Indicative measuring range (g/an)	Visual alarm
Low sensitivity ("B" on the device)	From 0 to 300 g/an	All the leds (8) for 300 g/an
Normal sensitivity ("Norm" on the device)	From 0 to 30 g/an	All the leds (8) for 30 g/an
High sensitivity ("H" on the device)	From 0 to 3 g/an	All the leds (8) for 3 g/an




#### REGLEMENTATIONS

The refrigerant gas detector complied with the EN 14624 standard that determines the following points:

- **Minimum threshold of sensitivity:**  
**Fixed :** < 1 g / year at 3 mm  
**In moving air :** 2 g / year, 2 cm / s at 3 mm
- **Minimum time of detection (1 g / year):** 1 second
- **Autozero:** 2 seconds
- **Recuperation time after exposition:** from 1 to 10 seconds (depending on detection level and threshold of sensitivity)

## SIZE



## MAINTENANCE

We realise the check, adjustment and maintenance of your devices to guarantee a constant quality level of your measurements. According to the quality assurances standards, we recommend a yearly checking. We recommend to check regularly that the nozzle of the detector and its filter are clean in order to guarantee the performances of the device.

## WARRANTY

Instruments have 1-year guarantee for any manufacturing defect (return to our After-Sales Service required for appraisal).

## SUPPLIED WITH

Devices are supplied with:

- Verification certificate
- Transport case
- Test sample containing refrigerant gas
- Filter



## ACCESSORIES

**CQD:** Magnetic protective housing



**MT 51:** ABS transport case



[www.kimo.fr](http://www.kimo.fr)

Distributed by :



**EXPORT DEPARTMENT**

Tel : + 33. 1. 60. 06. 69. 25 - Fax : + 33. 1. 60. 06. 69. 29

e-mail : [export@kimo.fr](mailto:export@kimo.fr)

**BELMET97**

Zagreb, Hrvatskog proljeća 34  
+385/01/29 59 900 (HR/CRO)  
prodaja - usluge mjerenja - servis  
[www.belmet97.hr](http://www.belmet97.hr)